Acrylic Folder



The **RH Acrylic Folder** is designed for heating acrylic sheet such as $Perspex^{TM}$, to make display stands for collection objects.

Features include:

- Easy to operate, just an on/off switch, a knob to control the heat time and a button to commence heating. When the button is pressed, the heating element switches on, and an indicator light comes on on the front of the body of the unit. The heating element is automati cally switched off by the timer. A small buzz is audible to indicate the acrylic sheet may be removed and bent to the desired angle
- The sheet thickness may vary from 2 8 mm.
- Sturdy outer casing of powder coated steel and anodized aluminum tops.

The RH Acrylic Folder operates from a standard earthed power outlet of 110 V, 16 A, 60 Hz or 230–240 V, 10 A, 50 Hz. RH Acrylic Folder meet the requirements of the CC regulation.

Standard fold length, 600 mm.

Specifications subject to change without notice.



rhe@RHConservationEng.com www.RHConservationEng.com